


**NOTE:**  
DIMENSIONS IN INCHES [mm]



## SPECIFICATIONS

PARAMETER	UNITS	
FERRULE ID	um	127
INSERTION LOSS	dB	≤0.3
DURABILITY (500 TIMES)	dB	≤0.3
OPERATING TEMPERATURE	°C	-40~+85
STORAGE TEMPERATURE	°C	-40~+85
TYPICAL CABLE OD	mm	Ø2.0

## FEATURES

- \* LC CONNECTORS ARE COMPLIANT TIA/EIA-640-10;  
LUCENT: 640-252-256
- \* PRODUCT QUALITY COMPLY WITH GR-326-CORE

PART#: GBLC2-D3-XX

### LENGTH (METERS)

01, 02, 03, 04, 05, 06, 07,  
08, 09, 10, 15, 20, 25, 30



**Allen Tel Products, Inc.**

30 TV5 DRIVE • HENDERSON, NV • 89014

**GBLC2-D3-XX LC TO LC DUPLEX  
MULTIMODE 50/125 (BLUE JACKET)**

