



SPECIFICATIONS

PARAMETER	UNITS	
FERRULE ID	um	125
INSERTION LOSS	dB	≤0.2
RETURN LOSS	dB	≤50
DURABILITY (500 TIMES)	dB	≤0.2
OPERATING TEMPERATURE	°C	-40~+85
STORAGE TEMPERATURE	°C	-40~+85
TYPICAL CABLE OD	mm	Ø2.0

FEATURES

- * LC CONNECTORS ARE COMPLIANT TIA/EIA-604-10 LUCENT 640-252-256
- * PRODUCT QUALITY COMPLY WITH GR-326-CORE

PART#: GBLC2-S1-XX

LENGTH (METERS)

01, 02, 03, 04, 05, 06, 07,
08, 09, 10, 15, 20, 25, 30



ALLEN TEL PRODUCTS, INC.

30 TV5 DRIVE • HENDERSON, NV • 89014

**GBLC2-S1-XX LC TO LC SIMPLEX
MULTIMODE 9/125 (YELLOW JACKET)**

