



## SPECIFICATIONS

PARAMETER	UNITS	
FERRULE ID	um	127
INSERTION LOSS	dB	≤0.3
DURABILITY (500 TIMES)	dB	≤0.3
OPERATING TEMPERATURE	°C	-40~+85
STORAGE TEMPERATURE	°C	-40~+85
TYPICAL CABLE OD	mm	Ø2.0

## FEATURES

- \* LC CONNECTORS ARE COMPLIANT TIA/EIA-640-10;  
LUCENT: 640-252-256
- \* PRODUCT QUALITY COMPLY WITH GR-326-CORE



**ALLEN TEL PRODUCTS, INC.**

30 TV5 DRIVE • HENDERSON, NV • 89014

**GBLCPT-S3X-XX**

**LC/PT DUPLEX MM 50/125 OM3 PIGTAIL**