



SPECIFICATIONS

PARAMETER	UNITS	
FERRULE ID	um	125
INSERTION LOSS	dB	≤0.2
RETURN LOSS	dB	≤50
DURABILITY (500 TIMES)	dB	≤0.2
OPERATING TEMPERATURE	°C	-40~+85
STORAGE TEMPERATURE	°C	-40~+85
TYPICAL CABLE OD	mm	Ø0.9

FEATURES

- * LC CONNECTORS ARE COMPLIANT TIA/EIA-604-10 LUCENT 640-252-256
- * PRODUCT QUALITY COMPLY WITH GR-326-CORE

PART#: GBLCPT-S1X-XX

TOTAL LENGTH



ALLEN TEL PRODUCTS, INC.

30 TV5 DRIVE • HENDERSON, NV • 89014

GBLCPT-S1X-XX

LC SIMPLEX SM 9/125 PIGTAIL