



SPECIFICATIONS

| PARAMETER | UNITS | |
|------------------------|-------|---------|
| FERRULE ID | um | 127 |
| INSERTION LOSS | dB | <0.3 |
| DURABILITY (500 TIMES) | dB | <0.2 |
| OPERATING TEMPERATURE | °C | -40~+85 |
| STORAGE TEMPERATURE | °C | -40~+85 |
| TYPICAL CABLE OD | mm | Ø0.9 |

FEATURES

- * LC CONNECTORS ARE COMPLIANT IEC 60874-14; TIA/EIA-604-3A.
- * PRODUCT QUALITY COMPLY WITH GR-326-CORE

PART#: GBLCPT-S4X-XX

TOTAL LENGTH



ALLEN TEL PRODUCTS, INC.

30 TV5 DRIVE • HENDERSON, NV • 89014

GBLCPT-S4X-XX

LC/PT SIMPLEX MM 50/125 OM3 PIGTAIL