



SPECIFICATIONS

PARAMETER	UNITS	
INSERTION LOSS	dB	<0.3 (<0.5 for MTRJ)
DURABILITY (500 TIMES)	dB	<0.3 (<0.5 for MTRJ)
OPERATING TEMPERATURE	°C	-40~+85
STORAGE TEMPERATURE	°C	-40~+85
TYPICAL CABLE OD	mm	ø1.8

FEATURES

- * MTRJ CONNECTORS ARE COMPLIANT IEC-60874-16; F12 (JIS C5981); TIA/EIA-604-12
- * SC CONNECTORS ARE COMPLIANT IEC 60874-14; FO4 (JIS C5973); TIA/EIA-640-3A
- * PRODUCT QUALITY COMPLY WITH GR-326-CORE
- * RoHS COMPLIANCE

PART#: GBMMC-D2-XX

XX = LENGTH IN METERS

01, 02, 03, 04, 05, 06, 07, 08, 09, 10, 15, 20, 25, 30



Allen Tel Products, Inc.

30 TV5 DRIVE • HENDERSON, NV • 89014

GBMMC-D2-XX MTRJ/MALE TO SC DUPLEX
MULTIMODE 62.5/125 (ORANGE JACKET)