



### SPECIFICATIONS

PARAMETER	UNITS	
FERRULE ID	um	125
INSERTION LOSS	dB	<0.3
DURABILITY (500 TIMES)	dB	<0.3
OPERATING TEMPERATURE	°C	-40~+85
STORAGE TEMPERATURE	°C	-40~+85
TYPICAL CABLE OD	mm	Ø2.0

### FEATURES

- \* SC CONNECTORS ARE COMPLIANT IEC 60874-14; F04 (JIS C5973); TIA/EIA-604-3A
- \* PRODUCT QUALITY COMPLY WITH GR-326-CORE

PART#: GBSCA2-D2-XX



**Allen Tel Products, Inc.**  
30 TV5 DRIVE • HENDERSON, NV • 89014

**GBSCA2-D2-XX ST TO SC DUPLEX  
SINGLEMODE 62.5/125 (ORANGE JACKET)**

