



## SPECIFICATIONS

PARAMETER	UNITS	
FERRULE ID	um	125
INSERTION LOSS	dB	≤0.2
RETURN LOSS	dB	≥50
DURABILITY (500 TIMES)	dB	≤0.2
OPERATING TEMPERATURE	°C	-40~+85
STORAGE TEMPERATURE	°C	-40~+85
TYPICAL CABLE OD	mm	Ø0.9

## FEATURES

- \* ST CONNECTORS ARE COMPLIANT IEC 60874-10; TIA/EIA-604-2.
- \* PRODUCT QUALITY COMPLY WITH GR-326-CORE



**ALLEN TEL PRODUCTS, INC.**

30 TV5 DRIVE • HENDERSON, NV • 89014

**GBSTPT-S1X-XX**  
**ST/PT SIMPLEX MM 9/125 PIGTAIL**