



SPECIFICATIONS

PARAMETER	UNITS	
FERRULE ID	um	125
INSERTION LOSS	dB	≤0.2
RETURN LOSS	dB	PC ≥50
DURABILITY (500 TIMES)	dB	≤0.2
OPERATING TEMPERATURE	°C	-40~+85
STORAGE TEMPERATURE	°C	-40~+85
TYPICAL CABLE OD	mm	Ø3.0

FEATURES

- * SC CONNECTORS ARE COMPLIANT IEC 60874-14; TIA/EIA-604-2.
- * PRODUCT QUALITY COMPLY WITH GR-326-CORE
- * CORNING TBII FIBER



ALLEN TEL PRODUCTS, INC.
30 TV5 DRIVE • HENDERSON, NV • 89014

GBSTUTBPT-S1-XX
ST SIMPLEX SM 9/125 PIGTAIL