



P1	P2
1	1
26	26
2	2
27	27
3	3
28	28
4	4
29	29
5	5
30	30
6	6
31	31
7	7
32	32
8	8
33	33

P1	P2
9	9
34	34
10	10
35	35
11	11
36	36
12	12
37	37
13	13
38	38
14	14
39	39
15	15
40	40
16	16
41	41

P1	P2
17	17
42	42
18	18
43	43
19	19
44	44
20	20
45	45
21	21
46	46
22	22
47	47
23	23
48	48
24	24
49	49
25	25
50	50

P/N	L	A
25-3-PX-5-180	1524	50.8
25-3-PX-10-180	3048	50.8
25-3-PX-15-180	4572	102
25-3-PX-20-180	6096	102
25-3-PX-25-180	7620	102
25-3-PX-30-180	9144	102
25-3-PX-40-180	12192	1.5% L
25-3-PX-50-180	15240	
25-3-PX-75-180	22860	
25-3-PX-100-180	30480	
25-3-PX-150-180	45720	
25-3-PX-200-180	60960	

ITEM	QTY	DESCRIPTION
7	2	SCREW: #4-40 * L13.8mm
6	1	DUSTPROOF COVER: BLUE
5	A/R	PVC TUBE
4	1	TOP PLASTIC SHELL: GRAY 180
3	1	BOTTOM PLASTIC SHELL: GRAY 180
2	1	CONN: 50P M GRAY
1	A/R	CABLE: 24AWG * 25P GRAY

**NOTES:**

- 100% PASS CONTINUITY TEST
- CAT3 RATED
- UL LISTING: E154502



Allen Tel Products, Inc.

**Allen Tel Products, Inc.**

30 TV5 DRIVE • HENDERSON, NV • 89014

**25-3-PX-XX-180**  
**MALE SINGLE END CONNECTORIZED CABLE**