



SPECIFICATIONS:

NO. OF CONDUCTORS: 8

CONDUCTOR MAT'L: AWG # 26 7 STRANDS, #35 BARE COPPER CONDUCTOR.

CONDUCTOR INSULATION: POLYPROPYLENE (P.P) DIAMETER: MAX .040, MIN, .035.

JACKET: POLYVINYLCHLORIDE (P.V.C.) THICKNESS .040 IN.

COLOR: SILVER SATIN.

VOLTAGE: 300 V

STANDARD LENGTHS

AT1007-K, 7 FT

AT1014-K 14 FT

AT1025-K 25 FT

OTHER LENGTHS

PER ORDER



ALLEN TEL PRODUCTS, INC.

30 TV5 DRIVE • HENDERSON, NV • 89014

AT10XX-K LINE CORDS