

MATERIAL:

PLASTIC BODY POLYCARBONATE (PC)

FLAME RATING - 94VO

CONTACT BLADE:

HIGH STRENGTH COPPER ALLOY

PLATING:

FIFTY MICRO INCHES OF GOLD SELECTIVELY
PLATED OVER 100 MICRO INCHES OF NICKEL.

ELECTRICAL:

DIELECTRIC WITHSTANDING VOLTAGE 500 VAC

INSULATION RESISTANCE 500 MEGOHMS

TERMINAL RESISTANCE 35 MILLIOHMS

TERMINAL RATING 250 VAC MAX AT 2 AMPS

MECHANICAL:

MINIMUM CONTACT FORCE - 100 GRAMS

INSERTION FORCE LESS THAN 5 LBS.


PULL OFF FORCE - 10 LBS. MIN.

DURABILITY - 200 MATING CYCLES

CORD PULL OFF FORCE - 15 LBS. MIN

FOR WIRE TYPE:

SOLID 22/24 GAGE WIRE



E121930 LR84410-5M



Allen Tel Products, Inc.

30 TV5 DRIVE • HENDERSON, NV • 89014

AT4X6SC-2224
MODULAR PLUG 4C6P