



CABLE SPECIFICATION

ITEM		SPEC.
CENTER CONDUCTOR	MATERIAL	BARE COPPER WIRE
	CONSTRUCTION mm/NO.	0.20mm/ 7C
	O.D. mm	0.20mm
INSIDE INSULATION	MATERIAL	PE
	O.D. mm	1.0 ±0.1*8F
	COLOR	REF.
PVC JACKET	MATERIAL	PVC
	O.D. mm	5.4 ±15
	COLOR	REF.

CHANNEL COMPARISON	CAT6	VIP 2000
INSERT LOSS (250MHz)	36.0db	34.0db
PS-NEAR END CROSS TALK(NEXT) (250MHz)	30.2db	34.0db
RETURN LOSS (250MHZ)	8.0db	10.0db
INDEPENDENTLY TESTED	NO	YES
POSITIVE PS-ACR (250 MHz)	NO	YES

NOTES:

1. 110 TO 110 PLUG CONFIGURATION
2. WHERE XX = 03, 05, 07, 10, 15 IN FEET.



Allen Tel Products, Inc.

30 TV5 DRIVE • HENDERSON, NV • 89014

**GB110PC645-XX CAT6
110 PATCH CORD**