



SPECIFICATIONS

PARAMETER	UNITS	
FERRULE ID	um	127
INSERTION LOSS	dB	≤0.3
DURABILITY (500 TIMES)	dB	≤0.3
OPERATING TEMPERATURE	°C	-40~+85
STORAGE TEMPERATURE	°C	-40~+85
TYPICAL CABLE OD	mm	Ø2.0

FEATURES

- * LC CONNECTORS ARE COMPLIANT TIA/EIA-640-10;
LUCENT: 640-252-256
- * PRODUCT QUALITY COMPLY WITH GR-326-CORE



ALLEN TEL PRODUCTS, INC.

30 TV5 DRIVE • HENDERSON, NV • 89014

GBLCPT-S3X-XX

LC/PT DUPLEX MM 50/125 OM3 PIGTAIL