



SPECIFICATIONS

PARAMETER	UNITS	
FERRULE ID	um	125
INSERTION LOSS	dB	≤0.3
DURABILITY (500 TIMES)	dB	≤0.3
OPERATING TEMPERATURE	°C	-40~+85
STORAGE TEMPERATURE	°C	-40~+85
TYPICAL CABLE OD	mm	Ø0.9

FEATURES

- * LC CONNECTORS ARE COMPLIANT IEC 60874-14; TIA/EIA-604-3A.
- * PRODUCT QUALITY COMPLY WITH GR-326-CORE

PART#: GBLCPT-S5X-XX

TOTAL LENGTH



ALLEN TEL PRODUCTS, INC.

30 TV5 DRIVE • HENDERSON, NV • 89014

GBLCPT-S5X-XX
LC/PC SIMPLEX MM 50/125
OM4 PIGTAIL (AQUA JACKET)