



SPECIFICATIONS

PARAMETER	UNITS	
FERRULE ID	um	127
INSERTION LOSS	dB	<0.3
DURABILITY (500 TIMES)	dB	<0.3
OPERATING TEMPERATURE	°C	-40~+85
STORAGE TEMPERATURE	°C	-40~+85
TYPICAL CABLE OD	mm	Ø3.0

FEATURES

- * SC CONNECTORS ARE COMPLIANT IEC 60874-14; F04 (JIS C5973); TIA/EIA-604-3A
- * PRODUCT QUALITY COMPLY WITH GR-326-CORE

PART#: GBLCT-D4-XX

LENGTH (METERS)
 01, 02, 03, 04, 05, 06, 07,
 08, 09, 10, 15, 20, 25, 30



Allen Tel Products, Inc.

30 TV5 DRIVE • HENDERSON, NV • 89014

**GBSC2-D4-XX 10Gb SC TO SC DUPLEX
 MULTIMODE 50/125 OM3 (AQUA JACKET)**