



## SPECIFICATIONS

PARAMETER	UNITS	
FERRULE ID	um	125
INSERTION LOSS	dB	<0.2
RETURN LOSS	dB	>50
DURABILITY (500 TIMES)	dB	<0.3
OPERATING TEMPERATURE	°C	-40~+85
STORAGE TEMPERATURE	°C	-40~+85
TYPICAL CABLE OD	mm	Ø3.0

PART#: GBSCA2-D1-XX

LENGTH PER ORDER

## FEATURES

- \* SC CONNECTORS ARE COMPLIANT IEC 60874-14; FO4 (JIS C5973); TIA/EIA-604-3A.
- \* PRODUCT QUALITY COMPLY WITH GR-326-CORE
- \* RoHS COMPLIANCE



**ALLEN TEL PRODUCTS, INC.**

30 TV5 DRIVE • HENDERSON, NV • 89014

**GBSCA2-D1-XX SC TO SC DUPLEX  
SINGLEMODE 9/125 (YELLOW JACKET)**

