



## SPECIFICATIONS

PARAMETER	UNITS	
FERRULE ID	um	125
INSERTION LOSS	dB	≤0.2
RETURN LOSS	dB	PC <sub>≥</sub> 50
DURABILITY (500 TIMES)	dB	≤0.2
OPERATING TEMPERATURE	°C	-40~+85
STORAGE TEMPERATURE	°C	-40~+85
TYPICAL CABLE OD	mm	Ø0.9

## FEATURES

- \* SC CONNECTORS ARE COMPLIANT IEC 60874-14; TIA/EIA-604-3A.
- \* PRODUCT QUALITY COMPLY WITH GR-326-CORE



ALLEN TEL PRODUCTS, INC.  
30 TV5 DRIVE • HENDERSON, NV • 89014

GBSCPT-S1X-XX  
SC SIMPLEX SM 9/125 PIGTAIL