



FEATURES

- * ST CONNECTORS ARE COMPLIANT IEC 60874-10; TIA/EIA-604-2
- * PRODUCT QUALITY COMPLY WITH GR-326-CORE
- * RoHS COMPLIANCE

PART#: GBST2-D1-XX
 XX = 01, 02, 03, 04, 05, 06, 07, 08, 09, 10,
 15, 20, 25, 30 METERS

SPECIFICATIONS

PARAMETER	UNITS	
FERRULE ID	um	125
INSERTION LOSS	dB	≤0.2
RETURN LOSS	dB	≥50
DURABILITY (500 TIMES)	dB	≤0.3
OPERATING TEMPERATURE	°C	-40~+85
STORAGE TEMPERATURE	°C	-40~+85
TYPICAL CABLE OD	mm	Ø2.0



**GBST2-D1-XX ST TO ST DUPLEX
 SINGLEMODE 9/125 (YELLOW JACKET)**