



## SPECIFICATIONS

PARAMETER	UNITS	
FERRULE ID	um	127
INSERTION LOSS	dB	≤0.3
DURABILITY (500 TIMES)	dB	≤0.3
OPERATING TEMPERATURE	°C	-40~+85
STORAGE TEMPERATURE	°C	-40~+85
TYPICAL CABLE OD	mm	Ø3.0

## FEATURES

- \* ST CONNECTORS ARE COMPLIANT IEC 60874-10;  
TIA/EIA-604-2
- \* PRODUCT QUALITY COMPLY WITH GR-326-CORE

PART#: GBST2-D2-XX

LENGTH (METERS)

01, 02, 03, 04, 05, 06, 07,  
08, 09, 10, 15, 20, 25, 30



ALLEN TEL PRODUCTS, INC.

30 TV5 DRIVE • HENDERSON, NV • 89014

GBST2-D2-XX ST TO ST DUPLEX  
MULTIMODE 62.5/125 (ORANGE JACKET)

