



SPECIFICATIONS

PARAMETER	UNITS	
FERRULE ID	um	125
INSERTION LOSS	dB	<0.3
DURABILITY (500 TIMES)	dB	<0.3
OPERATING TEMPERATURE	°C	-40~+85
STORAGE TEMPERATURE	°C	-40~+85
TYPICAL CABLE OD	mm	Ø2.0

FEATURES

- * ST CONNECTORS ARE COMPLIANT IEC 60874-10; TIA/EIA-604-2
- * SC CONNECTORS ARE COMPLIANT IEC 60874-14; F04 (JIS C5973); TIA/EIA-604-3A
- * PRODUCT QUALITY COMPLY WITH GR-326-CORE

PART#: GBSTA-SCA-D2-XX

LENGTH PER ORDER



Allen Tel Products, Inc.

30 TV5 DRIVE • HENDERSON, NV • 89014

**GBSTA-SCA-D2-XX ST TO SC DUPLEX
SINGLEMODE 62.5/125 (ORANGE JACKET)**

