



SPECIFICATIONS

| PARAMETER | UNITS | |
|------------------------|-------|---------|
| FERRULE ID | um | 127 |
| INSERTION LOSS | dB | ≤0.3 |
| DURABILITY (500 TIMES) | dB | ≤0.2 |
| OPERATING TEMPERATURE | °C | -40~+85 |
| STORAGE TEMPERATURE | °C | -40~+85 |
| TYPICAL CABLE OD | mm | Ø0.9 |

FEATURES

- * ST CONNECTORS ARE COMPLIANT IEC 60874-10; TIA/EIA-604-2.
- * PRODUCT QUALITY COMPLY WITH GR-326-CORE



ALLEN TEL PRODUCTS, INC.

30 TV5 DRIVE • HENDERSON, NV • 89014

GBSTPT-S2X-XX

ST/PT SIMPLEX MM 62.5/125 PIGTAIL