



PARAMETER	UNITS	
FERRULE ID	um	127
INSERTION LOSS	dB	≤0.3
DURABILITY (500 TIMES)	dB	≤0.2
OPERATING TEMPERATURE	°C	-40~+85
STORAGE TEMPERATURE	°C	-40~+85
TYPICAL CABLE OD	mm	Ø0.9

FEATURES

- * ST CONNECTORS ARE COMPLIANT IEC 60874-10; TIA/EIA-604-2.
- * PRODUCT QUALITY COMPLY WITH GR-326-CORE



ALLEN TEL PRODUCTS, INC.

30 TV5 DRIVE • HENDERSON, NV • 89014

GBSTPT-S3X-XX

ST/PT SIMPLEX MM 50/125 OM3 PIGTAIL